


**W-Series
WBB WMF2.5 BLZ**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**DCS marshalling**

Our innovative PRV terminal blocks for DCS marshalling featuring a PUSH IN connection and our multifunctional DCS marshalling terminals featuring a screw connection (WMF) not only save space in the panel; they also guarantee more effective signal transmission in process control systems.

General ordering data

Type	WBB WMF2.5 BLZ
Order No.	1142980000
Version	W-Series, Fixing bracket, dark beige, 5.08 mm
GTIN (EAN)	4032248925896
Qty.	10 pc(s).

Data sheet

W-Series WBB WMF2.5 BLZ

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	5.08 mm	Width (inches)	0.2 inch
Height	88.5 mm	Height (inches)	3.484 inch
Depth	44.5 mm	Depth (inches)	1.752 inch
Net weight	10.2 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	Mounting block	Rail	TS 35
---------	----------------	------	-------

Additional technical data

Snap-on	No
---------	----

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP