

Vocals / Speech
Instruments

WMS 40 MINI VocalSet

- Up to 30h playtime with one single AA battery
- Plug & Play
- Gain control on pocket transmitter
- Compatible with all AKG MicroMics
- Low battery indicator
- Smallest and lightest bodypack transmitter in its class



All WMS 40 MINI vocal and instrumental systems share the same brilliant sound and ease of use. Unique HDAP (High Definition Audio Performance) technology ensures the best possible, realistic sound at any time.

The status LEDs of the receiver SR40 mini show following information: ON/OFF, link LED RF OK and audio clip LED AF clip. The output gain from the 6,3mm jack output is controlled via the volume gain switch. The included SMPS (switched mode power supply) works from 110-240V and features EU/UK/US adapters.

The rugged handheld transmitter HT40 Mini offers a metal microphone cap and an ON/OFF/MUTE switch. The dynamic microphone capsule features a cardioids polar pattern.

Name	SKU	EAN				MHZ	UPC
WMS 40 MINI Vocal Set ISM1	3347X00030	90	02761	03158	4	863100	885038 03158 1
WMS 40 MINI Vocal Set ISM2	3347X00040	90	02761	03159	1	864375	885038 03159 8
WMS 40 MINI Vocal Set ISM3	3347X00050	90	02761	03160	7	864850	885038 03160 4
WMS 40 MINI Vocal Set US45A	3347X00060	90	02761	03161	4	660700	885038 03161 1
WMS 40 MINI Vocal Set US45B	3347X00070	90	02761	03162	1	661100	885038 03162 8
WMS 40 MINI Vocal Set US45C	3347X00080	90	02761	03163	8	662300	885038 03163 5



by HARMAN