



## MMX-4

Order No.: 24.1070

### PRODUCTINFOS

#### Miniature microphone mixer

- 4 mono microphone channels
- Output level control, peak LED
- Supplied without battery

### TECHNICAL SPECIFICATIONS

#### MMX-4

No. of channels	4
No. of inputs	4
Mic input	5 mV, 4 x 6.3 mm jack
Line input	-
CD input	-

**MMX-4**

Phono input	-
Tape (play)	-
Aux input	-
Insert input	-
effect return	-
Master output	100 mV, 1 x 6.3 mm jack
Record output	-
Monitor output	-
Booth output	-
Aux output	-
Insert output	-
effect send	-
Control room	-
Tape (rec)	-
Headphones	-
Gooseneck lamp	-
WiFi	-
USB	-
Frequency range	20-20,000 Hz
THD	<0,5%
S/N ratio	55 dB
Crosstalk	-
Equalizer bass	-
Equalizer midrange	-
Equalizer treble	-
equalizer	-
Talkover	-
Phantom power	-
Crossfader	-
Media player	-
Amplifier	-
Power supply	9 V battery or via optional power supply PSS-600E
Mains voltage	-
Mains frequency	-
Power consumption, operation	-
Alternative operating voltage	-
Alternative power supply	-

**MMX-4**

Admiss. ambient temp.	0-40 °C
Width	148 mm
Height	85 mm
Depth	55 mm
Rack spaces, RS	-
Weight	389 g

\* **Important Notice:** The retail prices shown here are non-binding recommendations that retailers can charge their customers. They are not part of any specific offer or advertisement. These prices include all charges as well as VAT, but do not cover any additional delivery and shipping costs. Our latest price lists for the retail market include all applicable delivery and payment terms for retailers.