

**Device markers
CC 30/60 O4MM MC NE GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



ClipCard O4mm MC are device markers in MultiCard format. These special versions can be easily fixed using screws or rivets through the 4.2 mm holes drilled on both sides.

General ordering data

Type	CC 30/60 O4MM MC NE GN
Order No.	1158820000
Version	Device markers, MultiCard, 30 x 60 mm, Polyamide 66, Colour: Green
GTIN (EAN)	4032248947522
Qty.	30 pc(s).

Device markers CC 30/60 04MM MC NE GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	30 mm	Width	60 mm
Height	1.2 mm	Net weight	4.633 g

General data

Application/manufacturer	With hole	Colour	Green
Material	Polyamide 66	Material colour according to resistance code	5
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Recommended industries	Machinery	UL 94 flammability rating	V-2

Device markers

Drill-hole diameter	4.2 mm	Humidity	≤ 60 %
---------------------	--------	----------	--------

Classifications

ETIM 3.0	EC001288	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

ROHS	Conform
------	---------

Downloads

M-Print® PRO configuration file	mc_cc_30_60-4_mcf.zip
---------------------------------	---------------------------------------