

**Device markers
CC 30/60 O4MM MC NE BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



ClipCard O4mm MC are device markers in MultiCard format. These special versions can be easily fixed using screws or rivets through the 4.2 mm holes drilled on both sides.

General ordering data

Type	CC 30/60 O4MM MC NE BL
Order No.	1158840000
Version	Device markers, MultiCard, 30 x 60 mm, Polyamide 66, Colour: Blue
GTIN (EAN)	4032248947294
Qty.	30 pc(s).

Device markers CC 30/60 04MM MC NE BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	30 mm	Width	60 mm
Height	1.2 mm	Net weight	4.6 g

General data

Application/manufacture	With hole	Colour	Blue
Material	Polyamide 66	Material colour according to resistance code	6
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Recommended industries	Machinery	UL 94 flammability rating	V-2

Device markers

Drill-hole diameter	4.2 mm	Humidity	≤ 60 %
---------------------	--------	----------	--------

Classifications

ETIM 3.0	EC001288	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

ROHS	Conform
------	---------

Downloads

M-Print® PRO configuration file	mc_cc_30_60-4_mcf.zip
---------------------------------	---------------------------------------