



ROADINGER Plastic rack KR-19, DD, black

Professional hard-sided flightcase for 483 mm units (19")

- Rugged and low-weight construction for effectors and controllers (max. weight 10 kg)
- Black scratchproof and shockproof ABS housing
- 2 removable covers (double-door version)
- Built-in rack rails (two-sided, looped)
- 2 slide bars (top)
- Stackable

No. 30106020.....	2 U
No. 30106024.....	4 U
No. 30106028.....	6 U
No. 30106032.....	8 U
No. 30106036.....	10 U

Technical specifications:

Device:	30106020	30106024	30106028	30106032	30106036	30106040
Maximum load:	10 kg	10 kg	10 kg	10 kg	10 kg	10 kg
Strength:	1.5 mm	1.5 mm	1.5 mm	1.5 mm	1.5 mm	1.5 mm
Outside dimensions (WxDxH):	approx. 145 x 545 x 570 mm	approx. 235 x 545 x 570 mm	approx. 340 x 535 x 570 mm	approx. 425 x 535 x 570 mm	approx. 550 x 570 x 520 mm	approx. 590 x 535 x 570 mm
Interior dimensions:						
Mounting width:	483 mm (19")	483 mm (19")	483 mm (19")	483 mm (19")	483 mm (19")	483 mm (19")
Mounting height:	approx. 90 mm (2 U)	approx. 190 mm (4 U)	approx. 300 mm (6 U)	approx. 370 mm (8 U)	approx. 450 mm (10U)	approx. 370 mm (12U)
Mounting depth:	approx. 540 mm	approx. 540 mm	approx. 540 mm	approx. 540 mm	approx. 540 mm	approx. 540 mm
Effective mounting depth:	approx. 420 mm	approx. 420 mm	approx. 420 mm	approx. 420 mm	approx. 420 mm	approx. 420 mm
Weight:	approx. 4 kg	approx. 5 kg	approx. 6 kg	approx. 7 kg	approx. 8 kg	approx. 8 kg