



ROADINGER Steel rack SR-19

The ultimate solution for all permanent installations

- Front and rear punched rack rails
- Integrated support rail in the inner side walls for heavy devices such as amplifiers
- Cage nuts, screws and plastic bolts included
- Mounting depth 41 cm
- Available in different height units (1 U = 44 mm)

No. 30103163	4 U
No. 30103164	6 U
No. 30103166	8 U
No. 30103168	10 U
No. 30103170	12 U
No. 30103171	14 U
No. 30103172	16 U
No. 30103190	18 U
No. 30103195	20 U
No. 30103196	22 U
No. 30103198	24 U
No. 30103210	30 U
No. 30103215	36 U
No. 30103220	40 U

Technical specifications:

Device:	4 U	6 U	8 U	10 U	12 U	16 U	18 U	20 U	24 U	30 U	36 U	40 U
Maximum load:	50 kg	50 kg	50	50 kg	50 kg	100 kg	100 kg	100 kg	100 kg	100 kg	150 kg	150 kg
Outside dimensions (LxWxH):	560 x 450 x 280 mm	560 x 450 x 340 mm	560 x 450 x 450 mm	560 x 450 x 580 mm	560 x 450 x 660 mm	560 x 450 x 840 mm	560 x 450 x 960 mm	560 x 450 x 1050 mm	560 x 450 x 1240 mm	560 x 450 x 1560 mm	560 x 450 x 1760 mm	560 x 450 x 1940 mm
Weight:	8.5 kg	10.5 kg	11 kg	15 kg	16 kg	20 kg	22.5 kg	25 kg	28 kg	34 kg	36 kg	46.5 kg



ROADINGER Steel cabinet SRT-19, 6U with door

Practical, stable and portable

- Lockable front door with acryl glass panel
- Removeable side and back panels
- 2 active built-in ceiling fans with switch
- 4 casters
- 4 plinth feet
- Flooring with openings for cable entry
- 1 mounting floor plate
- 2 front plates (1 U and 2 U)
- 6-fold multiple socket outlet with switch
- Available in different height units (1 U = 44 mm)

No. 30103288	6 U
No. 30103290	10 U
No. 30103292	12 U
No. 30103294	16 U
No. 30103300	20 U
No. 30103304	28 U
No. 30103320	35 U
No. 30103330	40 U

Technical specifications:

Device:	6 U	10 U	12 U	16 U	20 U	28 U	35 U	40 U
Maximum load:	100 kg	100 kg	100 kg	150 kg	150 kg	150 kg	200 kg	200 kg
Width:	600 mm	600 mm	600 mm	600 mm	600 mm	600 mm	600 mm	600 mm
Depth:	600 mm	600 mm	600 mm	600 mm	600 mm	600 mm	600 mm	600 mm
Outer height:	360 mm	720 mm	810 mm	890 mm	1160 mm	1510 mm	1820 mm	2060 mm
Weight:	18 kg	19 kg	36 kg	44 kg	60 kg	61 kg	55 kg	74 kg



No. 30103060

OMNITRONIC Rack stand

12U/10U adjustable on wheels

The solution for fixed installations

- Very rugged steel frame
- Swivel upper part with 12 U mounting facility for 483 mm units (19")
- Lower frame part with 10 U for units which require horizontal mounting
- 4 wheels, two of which are provided with a brake



No. 30103042

OMNITRONIC ELR-12/17 Notebook stand

Practical and flexible tool for on the road

- Solid steel frame for all standard notebook sizes 30-43 cm (12-17")
- Adjustable height: 24 cm, 26 cm, 28 cm and 30 cm

Technical specifications:

Maximum load:	5 kg
Minimum size (LxWxH):	265 x 235 x 235 mm
Maximum size (LxWxH):	265 x 235 x 315 mm
Weight:	1.4 kg