

MTA 30 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Power supplies from Weidmüller have long since proved their worth in supplying electrical modules. They can therefore be used safely in harsh industrial environments, in small businesses and in living areas, and have been granted international approvals. Weidmüller provides power supplies and additional components for industrial applications:

- Switched-mode power supply units
- DC/DC converters
- UPS control modules
- Electronic fuses

General ordering data

Type	MTA 30 BK
Order No.	1168970000
Version	Electronics housings, Mounting flange, Accessories
GTIN (EAN)	4032248960965
Qty.	45 pc(s).

MTA 30 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Length	68 mm	Length (inches)	2.677 inch
Width	30 mm	Width (inches)	1.181 inch
Height	8 mm	Height (inches)	0.315 inch
Weight	21.58 g	Net weight	20.089 g

Temperatures

Operating temperature, max.	100 °C	Operating temperature, min.	-50 °C
Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

General data

Weight	21.58 g
--------	---------

Classifications

ETIM 6.0	EC002625	eClass 6.2	27-18-09-90
eClass 7.1	27-18-09-90	eClass 8.1	27-18-09-90
eClass 9.0	27-18-28-07	eClass 9.1	27-04-92-90

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN CAT 4.3 ELECTR 15/16 EN CAT 2 PORTFOLIOGUIDE EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN
Engineering Data	EPLAN
Engineering Data	STEP

MTA 30 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Drawings**