

# Product Detail Page



## EDL-156

Order-No.: 16.1910

**Weatherproof PA ceiling speaker**, heat-resistant up to 100 °C. For applications in saunas and swimming pool areas.

- 100 V line technique
- 2-way system with dome tweeter
- Excellent sound
- White plastic housing
- Weatherproof speaker cone
- Tested according to ASTM B117 (400 h salt spray test)
- For a ceiling thickness from 2 to 25 mm

## Specifications

<b>Frequency range</b>	60-20,000 Hz
<b>Power capability, 100 V</b>	15/10/5/2.5/1.25 W <sub>RMS</sub>
<b>Power capability, 8 Ω</b>	-
<b>SPL (1 W/m)</b>	88 dB
<b>Max. rated SPL</b>	100 dB
<b>Type of speaker</b>	180
<b>Mounting cutout</b>	Ø 190 mm
<b>Mounting depth</b>	75 mm
<b>Admiss. ambient temp.</b>	-20 °C to +100 °C
<b>Dimensions</b>	Ø 226 mm x 100 mm
<b>Weight</b>	1.1 kg
<b>Other features</b>	-

