

W-Series, Accessories
WAP WDK10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WAP WDK10
Order No.	1186720000
Version	W-Series, Accessories, End plate
GTIN (EAN)	4050118024661
Qty.	20 pc(s).

**W-Series, Accessories
WAP WDK10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	85 mm	Width	1.5 mm
Height	60.85 mm	Net weight	6.88 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Version	End plate
---------	-----------

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC000886	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------