

**Industrial Ethernet
IE-PS-V14M-2SC-POF**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-117 ver.14 (PROFINET), metal incl. SC insert

General ordering data

Type	IE-PS-V14M-2SC-POF
Order No.	1191550000
Version	FO connector, Version 14, SC-RJ POF, IP 67
GTIN (EAN)	4032248974436
Qty.	10 pc(s).

Industrial Ethernet IE-PS-V14M-2SC-POF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	81.55 g
------------	---------

Temperatures

Operating temperature	-40 °C...+70 °C	Storage temperature
Installation temperature		

Downloads

Installation video	STEADYTEC® assembly instruction SC-RJ - POF IP67 connector_EN_HD.mp4
--------------------	---

General data

Colour	Miscellaneous	Description of article	Version 14, SC-RJ POF
Fibre type	POF	Housing main material	Zinc diecast
Insertion loss	≤ 1.0 dB	Plugging cycles	750
Protection degree	IP 67	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm		

Standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

Classifications

eClass 6.2	27-26-07-08	eClass 7.1	27-25-05-04
------------	-------------	------------	-------------

Approvals

ROHS	Conform
------	---------

**Industrial Ethernet
IE-PS-V14M-2SC-POF**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen**Dimensioned drawing**