

**TERMSERIES  
ZQV 1.5N/R12.8/10 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



TERMSERIES accessories include:

- Spare relay
- Base
- Partition plates
- Cross-connections
- Power-feed modules

**General ordering data**

Type	ZQV 1.5N/R12.8/10 GE
Order No.	<a href="#">1193700000</a>
Version	TERMSERIES, Cross-connector, No. of contacts: 10, AgNi, Continuous current: 17.5 A, UL: 10 A, Plug-in connection
GTIN (EAN)	4032248976447
Qty.	10 pc(s).

**TERMSERIES  
ZQV 1.5N/R12.8/10 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Width	119 mm	Net weight	6.6 g
-------	--------	------------	-------

**Temperatures**

Operating temperature	-40 °C...+60 °C	Storage temperature	-40 °C...+85 °C
-----------------------	-----------------	---------------------	-----------------

**Input**

Coil resistance		Pull-inrop-out current, typ.	
Pull-inrop-out typ.			

**Output**

Max. switching voltage, AC	250 V	Max. switching voltage, DC	250 V
Continuous current	17.5 A, UL: 10 A		

**Contact data**

No. of contacts	10	Contact material	AgNi
-----------------	----	------------------	------

**General data**

Wire connection method	Plug-in connection	UL 94 flammability rating	V-0
------------------------	--------------------	---------------------------	-----

**Connection data**

Wire connection method	Plug-in connection
------------------------	--------------------

**Classifications**

eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
------------	-------------	------------	-------------

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

PDF	<a href="#">Operating Instructions</a>
	<a href="#">3D Modell</a>