

**Cable glands  
VP M63 EXE MS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP M63 EXE MS
Order No.	<a href="#">1210950000</a>
Version	Cable glands, Blanking plug, Brass, nickel-plated, M 63, IP 68
GTIN (EAN)	4032248991976
Qty.	5 pc(s).

## Cable glands VP M63 EXE MS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	26 mm	Net weight	257 g
--------	-------	------------	-------

### Approvals

Approval for cable gland	II 2 GD, Ex d IIC, Ex e II, Ex tD
--------------------------	-----------------------------------

### General information

AF size 1	70 mm	External thread	M 63
Length of thread	19 mm	Material	Brass, nickel-plated
O-Ring	NBR	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Torque for cap nut, max.	20.1 Nm	Torque for cap nut, min.	13.4 Nm
Torque for connecting adapter, max.	67 Nm	Torque for connecting adapter, min.	33.5 Nm

### Classifications

eClass 6.2	27-14-91-12	eClass 7.1	27-14-91-12
------------	-------------	------------	-------------

### Product information

Descriptive text ordering data	Refer to the enclosed installation instructions for the tightening torque.
--------------------------------	--

### Approvals

ROHS	Conform
------	---------