

**Device markers
CC 85/54 O4MM MC NE GR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



ClipCard O4mm MC are device markers in MultiCard format. These special versions can be easily fixed using screws or rivets through the 4.2 mm holes drilled on both sides.

General ordering data

Type	CC 85/54 O4MM MC NE GR
Order No.	1248510000
Version	Device markers, MultiCard, 85 x 54 mm, Polyamide 66, Colour: Grey
GTIN (EAN)	4050118038668
Qty.	10 pc(s).

Device markers CC 85/54 04MM MC NE GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	85 mm	Width	54 mm
Height	1.2 mm	Net weight	12 g

General data

Application/manufacturer	With hole	Colour	Grey
Material	Polyamide 66	Material colour according to resistance code	8
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Recommended industries	Machinery	UL 94 flammability rating	V-2

Device markers

Drill-hole diameter	4.2 mm	Humidity	≤ 60 %
---------------------	--------	----------	--------

Classifications

eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
------------	-------------	------------	-------------

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_cc_85_54-4_mcf.zip
---------------------------------	---------------------------------------

Device markers CC 85/54 04MM MC NE GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Example of use



Product is similar to illustration