

**Clamping yoke
KLBUE 10-20 FM4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals.
These are available in different versions.

General ordering data

Type	KLBUE 10-20 FM4
Order No.	1252510000
Version	Clamping yoke, 50.5 mm
GTIN (EAN)	4032248112555
Qty.	10 pc(s).

Clamping yoke KLBUE 10-20 FM4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	50.5 mm	Width	25 mm
Height	40 mm	Net weight	36.9 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Wire clamp for cable diameter

Cable diameter, min.	10 mm	Cable diameter, max.	20 mm
----------------------	-------	----------------------	-------

System specifications

Product family	Clamping yoke	Mounting rail	TS 35
----------------	---------------	---------------	-------

Classifications

ETIM 3.0	EC000489	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-90		

Approvals

Approvals