

**W-Series
WTW 2.5-10 S**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WTW 2.5-10 S
Order No.	1266520000
Version	W-Series, Test adapter
GTIN (EAN)	4050118092585
Qty.	20 pc(s).

W-Series
WTW 2.5-10 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	1.5 mm	Width (inches)	0.059 inch
Height	56 mm	Height (inches)	2.205 inch
Depth	34 mm	Depth (inches)	1.339 inch
Net weight	3.175 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	Intermediate plate
---------	--------------------

Classifications

ETIM 4.0	EC000886	ETIM 5.0	EC000886
ETIM 6.0	EC002555	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33	eClass 8.1	27-14-11-33
eClass 9.0	27-14-11-48	eClass 9.1	27-14-11-48

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------