

**Accessories**  
**ETA 1170 21 8A****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	ETA 1170 21 8A
Order No.	<a href="#">1278780000</a>
Version	Accessories, Circuit breaker, 8 A
GTIN (EAN)	4050118091304
Qty.	5 pc(s).

## Accessories

### ETA 1170 21 8A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	9.8 mm	Width (inches)	0.386 inch
Height	22 mm	Height (inches)	0.866 inch
Depth	51.6 mm	Depth (inches)	2.031 inch
Net weight	10 g		

### Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

### Material data

Colour	black
--------	-------

### System specifications

Version	Fuse cartridge
---------	----------------

### Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

### Rating data

Rated voltage	28 V DC	Rated current	8 A
---------------	---------	---------------	-----

### Classifications

ETIM 6.0	EC000035	eClass 6.2	27-14-20-90
eClass 7.1	27-14-20-90	eClass 8.1	27-14-20-90
eClass 9.0	27-14-20-01	eClass 9.1	27-14-20-01

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN, WSCAD</a>
------------------	------------------------------