

**Accessories**  
**ETA 1180 01 0.25A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

|            |                                      |
|------------|--------------------------------------|
| Type       | ETA 1180 01 0.25A                    |
| Order No.  | <a href="#">1278860000</a>           |
| Version    | Accessories, Circuit breaker, 0.25 A |
| GTIN (EAN) | 4050118091441                        |
| Qty.       | 5 pc(s).                             |

## Data sheet

### Accessories ETA 1180 01 0.25A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 8.2 mm  | Width (inches)  | 0.323 inch |
| Height     | 24.4 mm | Height (inches) | 0.961 inch |
| Depth      | 52.3 mm | Depth (inches)  | 2.059 inch |
| Net weight | 10.6 g  |                 |            |

### Material data

|        |       |
|--------|-------|
| Colour | black |
|--------|-------|

### System specifications

|         |                |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

### Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

### Rating data

|               |         |               |        |
|---------------|---------|---------------|--------|
| Rated voltage | 64 V DC | Rated current | 0.25 A |
|---------------|---------|---------------|--------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC000886    | ETIM 6.0   | EC000035    |
| eClass 6.2 | 27-14-20-90 | eClass 7.1 | 27-14-11-33 |
| eClass 8.1 | 27-14-11-33 | eClass 9.0 | 27-14-20-01 |
| eClass 9.1 | 27-14-20-01 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                              |
|------------------|------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a> |
| Engineering Data | <a href="#">STEP</a>         |