

Accessories
ETA 1180 01 0.3A**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Product image**

Similar to illustration

Spring connection with tension clamp Technology

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	ETA 1180 01 0.3A
Order No.	1278870000
Version	Accessories, Circuit breaker, 0.3 A
GTIN (EAN)	4050118091472
Qty.	5 pc(s).

Data sheet

Accessories ETA 1180 01 0.3A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	8.2 mm	Width (inches)	0.323 inch
Height	24.4 mm	Height (inches)	0.961 inch
Depth	52.3 mm	Depth (inches)	2.059 inch
Net weight	10.6 g		

Material data

Colour	black
--------	-------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Rating data

Rated voltage	64 V DC	Rated current	0.3 A
---------------	---------	---------------	-------

Classifications

ETIM 5.0	EC000886	ETIM 6.0	EC000035
eClass 6.2	27-14-20-90	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP