

OMNIMATE Housing - series CH20M CH20M22 S PPP LGY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Superior efficiency, flexibility and design - the "standard tailor-made fit"

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customised design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M22 modular electronics housing is the standard format from amongst the different housing widths. It has the optimal width for most typical electronics applications.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- **Quicker installation** with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- **Maximum interference immunity** with ESD-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular". CH20M also stands for efficiency and innovation throughout design, production and use.

General ordering data

Type	CH20M22 S PPP LGY
Order No.	1296440000
Version	Electronics housings, OMNIMATE Housing - series CH20M Light Grey, Side element, Width: 22.5 mm
GTIN (EAN)	4050118094701
Qty.	10 pc(s).

**OMNIMATE Housing - series CH20M
CH20M22 S PPP LGY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	105.5 mm	Width	22.5 mm
Height	22.83 mm	Net weight	8.49 g

Material data

UL 94 flammability rating	V-0	Insulating material	PA 66 GF 30
Colour	Light Grey		

Classifications

eClass 6.2	27-18-08-02	eClass 7.1	27-18-27-02
------------	-------------	------------	-------------

Approvals

ROHS	Conform
------	---------

OMNIMATE Housing - series CH20M CH20M22 S PPP LGY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Zeichnungen

