

P-series TW PRV4 D-A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



Similar to illustration

DCS marshalling

Our innovative PRV terminal blocks for DCS marshalling featuring a PUSH IN connection and our multifunctional DCS marshalling terminals featuring a screw connection (WMF) not only save space in the panel; they also guarantee more effective signal transmission in process control systems.

General ordering data

Type	TW PRV4 D-A
Order No.	1297890000
Version	P-series, Separation plate, grey, 2 mm, printed, D-A, horizontally
GTIN (EAN)	4050118099515
Qty.	10 pc(s).

Data sheet

P-series TW PRV4 D-A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	2 mm	Width (inches)	0.079 inch
Height	70 mm	Height (inches)	2.756 inch
Depth	41.1 mm	Depth (inches)	1.618 inch
Net weight	4.75 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	125 °C		

Material data

Material	Polycarbonate	Colour	grey
UL 94 flammability rating	V-0		

System specifications

Version	printed, D-A, horizontally
---------	----------------------------

Additional technical data

Snap-on	Yes
---------	-----

Classifications

ETIM 3.0	EC000886	ETIM 5.0	EC000897
ETIM 6.0	EC000886	eClass 6.2	27-14-11-20
eClass 7.1	27-14-11-20	eClass 8.1	27-14-11-33
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-33

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Data sheet

**P-series
TW PRV4 D-A**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

