

**Device markers  
CC 15/60 O4MM MC NE GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



ClipCard O4mm MC are device markers in MultiCard format. These special versions can be easily fixed using screws or rivets through the 4.2 mm holes drilled on both sides.

**General ordering data**

|            |                                                                   |
|------------|-------------------------------------------------------------------|
| Type       | CC 15/60 O4MM MC NE GR                                            |
| Order No.  | <a href="#">1304060000</a>                                        |
| Version    | Device markers, MultiCard, 15 x 60 mm, Polyamide 66, Colour: Grey |
| GTIN (EAN) | 4050118103236                                                     |
| Qty.       | 40 pc(s).                                                         |

## Device markers CC 15/60 04MM MC NE GR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |        |
|--------|--------|------------|--------|
| Length | 15 mm  | Width      | 60 mm  |
| Height | 1.2 mm | Net weight | 3.15 g |

### General data

|                                   |              |                                              |        |
|-----------------------------------|--------------|----------------------------------------------|--------|
| Application/manufacture           | With hole    | Colour                                       | Grey   |
| Material                          | Polyamide 66 | Material colour according to resistance code | 8      |
| Operating temperature range, max. | 100 °C       | Operating temperature range, min.            | -40 °C |
| Recommended industries            | Machinery    | UL 94 flammability rating                    | V-2    |

### Device markers

|          |        |
|----------|--------|
| Humidity | ≤ 60 % |
|----------|--------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| eClass 6.2 | 27-14-91-29 | eClass 7.1 | 27-14-91-29 |
|------------|-------------|------------|-------------|

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|