

**SAK Series
HEVB ASK1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	HEVB ASK1
Order No.	1359500000
GTIN (EAN)	4008190039967
Qty.	50 pc(s).

SAK Series
HEVB ASK1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	15 mm	Width (inches)	0.591 inch
Height	8.2 mm	Height (inches)	0.323 inch
Depth	3.17 mm	Depth (inches)	0.125 inch
Net weight	0.3 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	black
----------	-------	--------	-------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 3.0	EC002255	ETIM 4.0	EC002255
ETIM 5.0	EC002255	ETIM 6.0	EC000149
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	21-04-50-03
eClass 9.1	21-01-90-90		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
------------------	-----------------------