

**RS 80**  
**AP 86**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



### Flexible - More flexible - Profilform

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

### General ordering data

|            |  |
|------------|--|
| Type       | AP 86  |
| Order No.  | <a href="#">1410960000</a>                         |
| Version    | End plate, RS 80 Orange, End plate, Width: 12.3 mm |
| GTIN (EAN) | 4008190122096                                      |
| Qty.       | 20 pc(s).  |

**RS 80**  
**AP 86**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |         |            |         |
|--------|---------|------------|---------|
| Length | 86.4 mm | Width      | 12.3 mm |
| Height | 62.2 mm | Net weight | 8.002 g |

### System characteristics

|                          |           |                   |       |
|--------------------------|-----------|-------------------|-------|
| Version                  | End plate | Cross-connection  | No    |
| Contact to terminal rail | No        | Protection degree | IP 20 |
| Encapsulation option     | No        |                   |       |

### Material data

|                           |        |                                       |       |
|---------------------------|--------|---------------------------------------|-------|
| UL 94 flammability rating | V-2    | Insulating material                   | PA 66 |
| Colour                    | Orange | Max. relative humidity during storage | 93 %  |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | UNSPSC     | 30-21-18-27 |
| eClass 5.1 | 27-14-11-33 | eClass 6.2 | 27-14-11-33 |
| eClass 7.1 | 27-14-11-33 |            |             |

### Approvals

Approvals



ROHS Conform