


**Conductor markers  
CLI C 2-4 GE/SW 8 CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                         |
|------------|-------------------------------------------------------------------------|
| Type       | CLI C 2-4 GE/SW 8 CD                                                    |
| Order No.  | <a href="#">1568261526</a>                                              |
| Version    | Conductor markers, 4 x 7 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4008190035457                                                           |
| Qty.       | 250 pc(s).                                                              |

## Conductor markers CLI C 2-4 GE/SW 8 CD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |       |      |
|------------|--------|-------|------|
| Length     | 4 mm   | Width | 7 mm |
| Height     | 8 mm   | Depth | 8 mm |
| Net weight | 0.21 g |       |      |

### General data

|                                              |             |                                   |                            |
|----------------------------------------------|-------------|-----------------------------------|----------------------------|
| Colour                                       | Yellow      | Colour of printing                | Black                      |
| Insulation cross-section, max.               | 10 mm       | Material                          | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4           | Operating temperature range, max. | 80 °C                      |
| Operating temperature range, min.            | -30 °C      | Orientation of print              | horizontal                 |
| Printed characters                           | Numbers     | Printing                          | 8                          |
| Printing method                              | Laser print | Recommended industries            | Process, Machinery         |
| Type of printing                             | Standard    | UL 94 flammability rating         | V-0                        |

### Conductor and cable markers

|                               |                    |                               |                     |
|-------------------------------|--------------------|-------------------------------|---------------------|
| Conductor O.D., max.          | 10 mm              | Conductor O.D., min.          | 4 mm                |
| Conductor cross-section, max. | 16 mm <sup>2</sup> | Conductor cross-section, min. | 2.5 mm <sup>2</sup> |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Conductor markers CLI C 2-4 GE/SW 8 CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen



Product is similar to illustration