

Z-series, Accessories
ZTA 1/ZA**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

General ordering data

Type	ZTA 1/ZA
Order No.	1609050000
Version	Test adapter, Rated control voltage:
GTIN (EAN)	4008190206543
Qty.	25 pc(s).

Z-series, Accessories ZTA 1/ZA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	31.5 mm	Width	5.1 mm
Height of lowest version	73.1 mm	Net weight	7.36 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Installation advice	Direct mounting	Version	For the terminals
---------------------	-----------------	---------	-------------------

Clampable wires (rated connection)

Type of connection	Plug-in connection	Stripping length	6 mm
Clamping range, rated connection, min.	0.5 mm ²	Clamping range, rated connection, max.	1.5 mm ²
Tightening torque, min.	0.3 Nm	Tightening torque, max.	0.3 Nm
Wire connection cross section, solid core, max. rated connection	0.5 mm	Wire connection cross section, solid core max. rated connection	1.5 mm
Wire connection cross section, finely stranded, max.	1.5 mm	Wire connection cross-section, finely stranded, min.	0.5 mm
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	1.5 mm

Disconnect terminals

Tightening torque, max.	0.3 Nm	Tightening torque, min.	0.3 Nm
-------------------------	--------	-------------------------	--------

Rated data

Rated cross-section	1.5 mm ²	Rated voltage	250 V
Rated current	9 A		

Material data

Material	Polyamide 66	Colour	Black
UL 94 flammability rating	V-2		

System specifications

Product family	Z-series, Accessories	Type of connection	Plug-in connection
----------------	-----------------------	--------------------	--------------------

Classifications

ETIM 3.0	EC002255	UNSPSC	30-21-18-01
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14

Datenblatt**Z-series, Accessories
ZTA 1/ZA**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Approvals**

Approvals



ROHS

Conform

Downloads

DXF	22247_ZTA_1-ZA_DXF.dxf
STEP	1609050000_22247_ZTA_1_ZA_STP.stp