

**Accessories**  
**ZTA 2 ZDU4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	ZTA 2 ZDU4
Order No.	<a href="#">1609060000</a>
Version	Accessories, Test adapter, 9 A
GTIN (EAN)	4008190466220
Qty.	25 pc(s).

**Accessories**  
**ZTA 2 ZDU4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	6.1 mm	Width (inches)	0.24 inch
Height	31.5 mm	Height (inches)	1.24 inch
Depth	73.1 mm	Depth (inches)	2.878 inch
Net weight	8.56 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	Polyamide 66	Colour	black
UL 94 flammability rating	V-2		

**System specifications**

Version	For the terminals	Number of levels	1
No. of clamping points per level	1		

**Additional technical data**

Installation advice	Direct mounting	With snap-in pegs	No
---------------------	-----------------	-------------------	----

**Conductors for clamping (rated connection)**

Clamping range, max.	1.5 mm <sup>2</sup>	Clamping range, min.	0.5 mm <sup>2</sup>
Number of connections	1	Stripping length	6 mm
Tightening torque, max.	0.3 Nm	Tightening torque, min.	0.3 Nm
Type of connection	Plug-in connection	Wire connection cross section, finely stranded, max.	1.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	1.5 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

**Dimensions**

Pitch in mm (P)	6 mm	Height with TS 35	103.5 mm
-----------------	------	-------------------	----------

**Rating data**

Rated cross-section	1.5 mm <sup>2</sup>	Rated voltage	250 V
Rated current	9 A		

**Accessories**  
**ZTA 2 ZDU4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Classifications**

ETIM 3.0	EC002255	ETIM 4.0	EC002255
ETIM 5.0	EC002255	ETIM 6.0	EC002555
UNSPSC	30-21-18-01	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14	eClass 8.1	27-14-11-48
eClass 9.0	27-14-11-48	eClass 9.1	27-14-11-48

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>