



NOTES:

1. MATERIALS

1.1 CABLE: [(7/0.12CCS+PVC)*5+7/0.12CCS+AM+PVC4.5]

OD: $\phi 4.5 \pm 0.15$ mm.

1.2 P1~P2: DIN 5PIN PULG, SOLDER TYPE, BLACK PBT INSULATION, TIN PLATED CONTACTS, NICKEL PLATED SHELL,

1.3 HOOD MOLDED BLACK PVC.

2. TESTING: 100% OPEN AND SHORT TEST.

3. PACKING: 50123 EACH CABLE IN A HEAT SEAL TYPE BLISTER(T12), WITH A PRINTED CARD.

50066 EACH CABLE IN A BLISTER(NT15), WITH A PRINTED CARD.

4. ALL MATERIAL BE ROHS AND REACH COMPLIANT.

PIN OUT

P/N CHART

P/N	L
50123	1500L ²³ MM
50066	5000L ¹⁵ MM



DIN 5P PULG
SOLDER SIDE

P1 (DIN5P)

1	GROUND WIRE
2	
3	
4	
5	

P2 (DIN5P)

1
2
3
4
5

DRAWING APPROVED _____ DATE: _____

SAMPLE APPROVED PER _____ DATE: _____
DRAWING SPECIFICATIONS

PROPRIETARY & CONFIDENTIAL. THIS DOCUMENT MAY NOT BE COPIED, OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE WRITTEN CONSENT OF NINGBO SHIP GROUP CARF ASSEMBLY CO., LTD.