


max resistance of the inner wire=7.5 Ohm

PIN OUT
P1 (MD4M) P2 (MD4M)

P/N CHART

P/N	L
50018	2.0M
50130	10.0M



NOTES:

1. MATERIALS

1.1 CABLE: [(7/0.12CCS+PVC+28/0.12CCA+PVC)*2+BLACK PVC]
OD: $\phi 5.5 \pm 0.2$ mm.

1.2 P1&P2: MINI DIN 4PIN PULG, SOLDER TYPE,
BLACK PBT INSULATION, TIN PLATED CONTACTS,
NICKEL PLATED SHELL.

1.3 HOOD MOLDED BLACK AND YELLOW PVC.

2. TESTING: 100% OPEN AND SHORT TEST.

3. PACKING: 50018 EACH CABLE IN A BLISTER(NT13),
WITH A PRINTED CARD.
50130 EACH CABLE IN A HEAT SEAL TYPE BLISTER(T15),
WITH A PRINTED CARD.

4. ALL MATERIAL BE ROHS COMPLIANT.

DRAWING APPROVED _____ DATE: _____
SAMPLE APPROVED PER DRAWING SPECIFICATIONS _____ DATE: _____

	mm	TITLE	
SCALE	NONE	MD4P PLUG/MD4P PLUG	
SHEET	1/1	CUS. NAME	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED		CUS. P/N	
.X ± 0.3	.XX \pm	SEE THE 'P/N CHART'	ENG. _____ DATE _____
.XXX \pm	ANGLES \pm	DRAWING NO.	CHECKED _____ DATE _____
REV. 00	CUS. REV. 00	AV-0908060	APPROVED _____ DATE _____

00	NEW ISSUE	2009-8-08
REV.	MODIFY DESCRIPTION	DATE