

- Electrical Test:
- 1.100% TEST OPEN SHORT MIS-WIRE.
  - 2.CONTACT RESISTANCE:3Ω MAX.
  - 3.INSULATION RESISTANCE:5MΩ MIN.
  - 4.HI-POT:300V DC/10MS.
  - 5.Real Test Passed 1920\*\*1080P 60HZ.
  - 6.Real Test Not Twinkling,Double Vision and Decolor.





D	45P PVC BLACK	G
C	HDMI D MALE (BLACK INSULATION GOLD PLATED 1U <sub>9</sub> )	1 PCS
B	HDMI A MALE (BLACK INSULATION GOLD PLATED 1U <sub>9</sub> )	1 PCS
A	NON-UL(92#*1P+AL)*5+32#*4C+AD OD:4.2mm BLACK COLOR PVC JACKET CABLE PRINTING:HIGH SPEED HDMI™ CABLE WITH ETHERNET	1 PCS
F	PRODUCT SPECIFICATIONS	Quantity Unit
NUMBER	BOM.NO	

G	新增線上CE貼紙/更新貼紙	2019-11-21
F	更新版本	2019-09-17
E	增加裝箱方式圖(注意裝箱時吊牌需反折在繞線圈內)	2017-02-28
VER	REVISE	DATE

Company: CONRAD


REALLY USEFUL  
ELECTRONICS INC.

Item	325240
Draw	Quodile Date: 2015.07.22
Approval	
Maker	F16 BOM.NO.:12873
Sample NO.	Drawings of 1 (2) Proportion: 1:1 Unit(mm) A4



吊牌反折後裝入紙箱  
吊牌需可以自由轉動  
所以吊牌不能鎖太緊

**\*裝箱時請小心放置,不可掛傷線材\***  
150PCS/CARTON(45\*34\*28CM) + 防水袋



D	取消PE袋單POS包裝	2017-02-23
C	PE袋增加環保標	2017-01-21
B	revise the pin assignment and length	2016-03-01
VER.A	REVISE	DATE

Company: CONRAD

Item	325240	
Draw	<i>Quoddi</i>	Date: 2015.07.22
Approval		
Maker	F16	BOM.NO.:12873
Sample NO.		

REALLY USEFUL  
ELECTRONICS INC.