

tonar

banana



Tonar Banana professional DISCO cartridge SPECIFICATIONS

Weight	16 g
Type of stylus	0,7 mil spherical diamond
Frequency response	20 - 20.000 Hz 20 - 15.000 Hz \pm 1 dB
Output voltage at 1000 Hz per 5 cm/sec	5 mV
Channel separation at 1000 Hz	20 dB
Channel balance at 1000 Hz	2 dB
Dynamic compliance horizontal / vertical	8/8 μ m/mN
Recommended tracking force	40 mN (4g)
Tracking force range	30 - 50 mN (3 - 5g)
Tracking ability at 315 Hz (lateral)	70 μ m
Vertical tracking angle	20°
FIM distortion	1.8%
DC resistance	600 ohm
Recommended load resistance	47 Kohm
Recommended load capacitance	400 pF
Cartridge mounting system	suitable for SME-type arm only
Replacement stylus	tonar nr. 1812



PRODUCT OF:
TONAR International b.v.
Beeldschemweg 5 unit 1
3821 AH AMERSFOORT - HOLLAND
FAX +31 33 4560544
TEL +31 33 4554511



banana

tonar