

**Terminal markers
ESO 5 S DIN A4-BOGEN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The various connector markers from Weidmüller enable users to solve virtually every labelling task on all types of lines. Whether several lines of labelling, ready-to-use markers with standard printing, or individual labelling, whether white or coloured markers or common designations at the clamping points, the comprehensive range of products represent the easy, quick and clear answer to every marking task.

General ordering data

Type	ESO 5 S DIN A4-BOGEN
Order No.	1631920000
Version	Terminal markers, 40 x 7 mm, Paper, Colour: White
GTIN (EAN)	4008190206673
Qty.	10 pc(s).

Terminal markers ESO 5 S DIN A4-BOGEN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	40 mm	Width	7 mm
Height	1 mm	Net weight	10.8 g

General data

Colour	White	Material	Paper
Material colour according to resistance code	9	Number per sheet	140
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	HB		

Connector markers

Pitch in mm (P)	5 mm
-----------------	------

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_eso_5_s_mcf.zip
---------------------------------	-------------------------------------