

**W-Series, Accessories  
WTA 1/ZA WDU1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm<sup>2</sup> to 300 mm<sup>2</sup> - means that you have diverse options for your applications at your disposal.  
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

**General ordering data**

Type	WTA 1/ZA WDU1.5
Order No.	<a href="#">1632300000</a>
Version	W-Series, Accessories, Test adapter
GTIN (EAN)	4008190257354
Qty.	25 pc(s).

## W-Series, Accessories WTA 1/ZA WDU1.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	66.1 mm	Width	5 mm
Height of lowest version	98.2 mm	Net weight	12.56 g

### Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

### Clampable wires (additional connection)

Clamping range, further connection, max.	1.5 mm <sup>2</sup>	Rated cross-section, further connection	1.5 mm <sup>2</sup>
--	---------------------	---	---------------------

### Clampable wires (rated connection)

Type of connection	Screw connection	Stripping length	6 mm
Number of connections	1	Clamping screw	M 2.5
Tightening torque, min.	0.3 Nm	Tightening torque, max.	0.3 Nm
Wire connection cross section, solid core, max. rated connection	0.5 mm <sup>2</sup>	Wire connection cross section, solid core max. rated connection	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	1.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded, min.	1 mm <sup>2</sup>
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	1.5 mm <sup>2</sup>

### Rated data

Rated cross-section	1.5 mm <sup>2</sup>	Rated voltage	250 V
Rated current	6 A		

### Material data

Material	PA 66	Colour	Black
UL 94 flammability rating	V-2		

### System specifications

Product family	W-Series, Accessories	Type of connection	Screw connection
Number of connections	1		

### Classifications

ETIM 3.0	EC002255	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

### Product information

Descriptive text technical data	Rated current 6 A
---------------------------------	-------------------

**Datenblatt**

**W-Series, Accessories**  
**WTA 1/ZA WDU1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Technische Daten**

**Approvals**

---

ROHS	Conform
------	---------

---