

**W-Series, Accessories
WTA 2/ZA WDU2.5-10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WTA 2/ZA WDU2.5-10
Order No.	1632330000
Version	W-Series, Accessories, Test adapter
GTIN (EAN)	4008190257330
Qty.	25 pc(s).

W-Series, Accessories WTA 2/ZA WDU2.5-10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	66.1 mm	Width	5 mm
Height of lowest version	107.6 mm	Net weight	8.71 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Clampable wires (additional connection)

Clamping range, further connection, max.	1.5 mm ²	Rated cross-section, further connection	1.5 mm ²
--	---------------------	---	---------------------

Clampable wires (rated connection)

Type of connection	Screw connection	Stripping length	6 mm
Number of connections	1	Clamping screw	M 2.5
Tightening torque, min.	0.3 Nm	Tightening torque, max.	0.3 Nm
Wire connection cross section, solid core, max. rated connection	0.5 mm ²	Wire connection cross section, solid core max. rated connection	1.5 mm ²
Wire connection cross section, finely stranded, max.	1.5 mm ²	Wire connection cross-section, finely stranded, min.	1 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	1.5 mm ²

Rated data

Rated cross-section	1.5 mm ²	Rated voltage	250 V
Rated current	6 A		

Material data

Material	PA 66	Colour	Black
UL 94 flammability rating	V-2		

System specifications

Product family	W-Series, Accessories	Type of connection	Screw connection
Number of connections	1		

Classifications

ETIM 3.0	EC002255	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

Product information

Descriptive text technical data	Rated current 6 A
---------------------------------	-------------------

Datenblatt**W-Series, Accessories
WTA 2/ZA WDU2.5-10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Approvals**

ROHS	Conform
------	---------

Downloads

DXF	21837_WTA_2-ZA_WDU2.5-10_DXF.dxf
-----	--

STEP	1632330000_21837_WTA_2_STP.stp
------	--

[3D Modell](#)