

**Terminal markers
ESO 5 POLY.WEISS A4-BOG.**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The halogen-free, transparent pocket of the **WKM** offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.

The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking.

Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

General ordering data

Type	ESO 5 POLY.WEISS A4-BOG.
Order No.	1670370000
Version	Terminal markers, 40 x 16.5 mm, Polyester, PVC-free, Colour: White
GTIN (EAN)	4008190430696
Qty.	10 pc(s).

Terminal markers ESO 5 POLY.WEISS A4-BOG.

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	40 mm	Width	16.5 mm
Height	1 mm	Net weight	13.5 g

General data

Colour	White	Material	Polyester, PVC-free
Material colour according to resistance code	9	Number per sheet	60
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	HB		

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file [lab_eso_5_poly_mcf.zip](#)