

**Terminal markers
ESO 5 POLY.GELB A4-BOG.**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The various connector markers from Weidmüller enable users to solve virtually every labelling task on all types of lines. Whether several lines of labelling, ready-to-use markers with standard printing, or individual labelling, whether white or coloured markers or common designations at the clamping points, the comprehensive range of products represent the easy, quick and clear answer to every marking task.

General ordering data

Type	ESO 5 POLY.GELB A4-BOG.
Order No.	1670380000
Version	Terminal markers, 40 x 16.5 mm, Polyester, PVC-free, Colour: Yellow
GTIN (EAN)	4008190430702
Qty.	10 pc(s).

**Terminal markers
ESO 5 POLY.GELB A4-BOG.**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	40 mm	Width	16.5 mm
Height	1 mm	Net weight	13.7 g

General data

Colour	Yellow	Material	Polyester, PVC-free
Material colour according to resistance code	4	Number per sheet	60
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	HB		

Connector markers

Pitch in mm (P)	5 mm
-----------------	------

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_eso_5_poly_mcf.zip
---------------------------------	--