

Device markers
LM MT300 25.4X12.7 SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Type	LM MT300 25.4X12.7 SI
Order No.	1686390001
Version	Device markers, Label, 25.4 x 12.7 mm, Polyester, PVC-free, Colour: Silver
GTIN (EAN)	4008190493967
Qty.	10 pc(s).

Device markers LM MT300 25.4X12.7 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	25.4 mm	Width	12.7 mm
Net weight	12.4 g		

General data

Adhesive	Acrylate adhesive	Colour	Silver
Material	Polyester, PVC-free	Number per sheet	147
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Printing method	Laser print	UL 94 flammability rating	HB
UL 969 flammability rating	Yes		

Classifications

ETIM 3.0	EC001288	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_lm_mt300_25-4x12-7_mcf.zip
---------------------------------	--