

**Cable markers
WSM 10 T**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**WSM small plates**

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

General ordering data

Type	WSM 10 T
Order No.	1712501676
Version	Cable markers, 5.5 x 9.9 mm, Stainless steel 1.4404, Colour: Silver
GTIN (EAN)	4008190947477
Qty.	200 pc(s).

Cable markers WSM 10 T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	5.5 mm	Width	9.9 mm
Height	0.3 mm	Depth	0.3 mm
Net weight	0.15 g		

General data

Colour	Silver	Material	Stainless steel 1.4404
Operating temperature range, max.	500 °C	Operating temperature range, min.	-80 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	T	Type of printing	Standard

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform