

## Cable markers WSM 10 Å

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



### WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ,, ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

### General ordering data

Type	WSM 10 Å
Order No.	<a href="#">1712501700</a>
Version	Cable markers, 5.5 x 9.9 mm, Stainless steel 1.4404, Colour: Silver
GTIN (EAN)	4032248492619
Qty.	200 pc(s).

**Cable markers  
WSM 10 Å**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**
**Dimensions and weights**

Length	5.5 mm	Width	9.9 mm
Height	1 mm	Net weight	0.15 g

**General data**

Colour	Silver	Material	Stainless steel 1.4404
Operating temperature range, max.	500 °C	Operating temperature range, min.	-80 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	Å	Type of printing	Standard

**Conductor and cable markers**

Conductor cross-section, max.	500 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Halogen	No		

**Classifications**

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

**Approvals**

Approvals	
ROHS	Conform