

**Conductor markers
VT SF 2/12 MC NE WS V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 2/12 MC NE WS V0
Order No.	1718480001
Version	Conductor markers, MultiCard, 12 x 3.6 mm, Polyamide 66, Colour: White
GTIN (EAN)	4008190349530
Qty.	800 pc(s).

Conductor markers VT SF 2/12 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	12 mm	Width	3.6 mm
Height	3.65 mm	Depth	3.5 mm
Net weight	0.236 g		

General data

Colour	White	Material	Polyamide 66
Material colour according to resistance code	9	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Size of labelling field	12x3.6 mm
Type of printing	blank	UL 94 flammability rating	V-0

Conductor and cable markers

Conductor O.D., max.	2.9 mm	Conductor O.D., min.	2.2 mm
Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.75 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file [mc_sf_2_12_mcf.zip](#)