

**Conductor markers
VT SF 3/12 MC NE GE V0**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 3/12 MC NE GE V0
Order No.	1718490004
Version	Conductor markers, MultiCard, 12 x 4.6 mm, Polyamide 66, Colour: Yellow
GTIN (EAN)	4008190349639
Qty.	640 pc(s).

Conductor markers VT SF 3/12 MC NE GE V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	12 mm	Width	4.6 mm
Height	4.8 mm	Depth	4.8 mm
Net weight	0.213 g		

General data

Colour	Yellow	Material	Polyamide 66
Material colour according to resistance code	4	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Size of labelling field	12x4.6 mm
Type of printing	blank	UL 94 flammability rating	V-0

Conductor and cable markers

Conductor O.D., max.	3.7 mm	Conductor O.D., min.	3 mm
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_sf_3_12_mcf.zip
---------------------------------	------------------------------------