

**Cable glands  
VP 48-K54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For sealing surplus threaded holes to maintain the IP  
class of protection

**General ordering data**

|            |                                                                              |
|------------|------------------------------------------------------------------------------|
| Type       | VP 48-K54                                                                    |
| Order No.  | <a href="#">1719260000</a>                                                   |
| Version    | Cable glands, Blanking plug, Polyamid 6 (PA6 - GF30), RAL 7035, PG 48, IP 54 |
| GTIN (EAN) | 4008190352516                                                                |
| Qty.       | 5 pc(s).                                                                     |

## Cable glands VP 48-K54

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |       |            |      |
|--------|-------|------------|------|
| Length | 16 mm | Net weight | 24 g |
|--------|-------|------------|------|

### General information

|                                   |                           |                                   |          |
|-----------------------------------|---------------------------|-----------------------------------|----------|
| Cable gland                       | PG                        | Colour code                       | RAL 7035 |
| DIN                               | DIN 46320 (for PG thread) | External thread                   | PG 48    |
| Head diameter                     | 69 mm                     | Length of thread                  | 12 mm    |
| Material                          | Polyamid 6 (PA6 - GF30)   | Operating temperature range, max. | 100 °C   |
| Operating temperature range, min. | -40 °C                    | Protection degree with GWDR       | IP 65    |
| UL 94 flammability rating         | V-2                       |                                   |          |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000032    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-91-10 | eClass 6.2 | 27-14-91-10 |
| eClass 7.1 | 27-14-91-10 |            |             |

### Product information

|                                 |                                                                                                             |
|---------------------------------|-------------------------------------------------------------------------------------------------------------|
| Descriptive text ordering data  | Other versions available on request. The sealing plugs must be tightened "hand-tight" with the screwdriver. |
| Descriptive text technical data | Optional sealing ring                                                                                       |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|