GWDR PO (flat gasket - polyethylene)
GWDR PG11-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR PG11-PO
Order No.	1719460000
Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 11, Polyethylene
GTIN (EAN)	4008190352714
Qty.	100 pc(s).

GWDR PO (flat gasket - polyethylene)
GWDR PG11-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.155 g

Width

Thickness	2 mm

General information

Cable glands	PG	Diameter of sealing ring	22.5 mm
External thread	PG 11	Inside diameter D2	18.6 mm
Material	Polyethylene	O.D.	22.5 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Sealing	PE-HD	Thickness	2 mm

Classifications

ETIM 3.0	EC000781	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	31-16-18-18	eClass 5.1	23-07-90-90
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-43-03-19
eClass 9.1	27-14-44-90		

Approvals

ROHS	Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

GWDR PO (flat gasket - polyethylene)
GWDR PG11-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

