

**GWDR PO (flat gasket - polyethylene)
GWDR PG21-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR PG21-PO
Order No.	1719490000
Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 21, Polyethylene
GTIN (EAN)	4008190352752
Qty.	100 pc(s).

GWDR PO (flat gasket - polyethylene)
GWDR PG21-PO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight 0.52 g

Width

Thickness 3 mm

General information

Cable glands	PG	Diameter of sealing ring	33.5 mm
External thread	PG 21	Inside diameter D2	28.3 mm
Material	Polyethylene	O.D.	33.5 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Sealing	PE-HD	Thickness	3 mm

Classifications

ETIM 3.0	EC000781	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	31-16-18-18	eClass 5.1	23-07-90-90
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-43-03-19
eClass 9.1	27-14-44-90		

Approvals

ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP

GWDR PO (flat gasket - polyethylene) **GWDR PG21-PO**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

