

**GWDR NP (flat gasket - neoprene)  
GWDR PG9-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

**General ordering data**

|            |                                                                |
|------------|----------------------------------------------------------------|
| Type       | GWDR PG9-NP                                                    |
| Order No.  | <a href="#">1719550000</a>                                     |
| Version    | GWDR NP (flat gasket - neoprene), Sealing ring, PG 9, Neoprene |
| GTIN (EAN) | 4008190352813                                                  |
| Qty.       | 100 pc(s).                                                     |

**GWDR NP (flat gasket - neoprene)**  
**GWDR PG9-NP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**
**Dimensions and weights**

Net weight 0.36 g

**Width**

Thickness 1.2 mm

**General information**

|                                   |          |                                   |        |
|-----------------------------------|----------|-----------------------------------|--------|
| Cable glands                      | PG       | Diameter of sealing ring          | 21 mm  |
| External thread                   | PG 9     | Inside diameter D2                | 14 mm  |
| Material                          | Neoprene | O.D.                              | 21 mm  |
| Operating temperature range, max. | 100 °C   | Operating temperature range, min. | -30 °C |
| Thickness                         | 1.2 mm   |                                   |        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000781    | ETIM 4.0   | EC000441    |
| ETIM 5.0   | EC000441    | ETIM 6.0   | EC000441    |
| UNSPSC     | 31-16-18-18 | eClass 5.1 | 23-07-90-90 |
| eClass 6.2 | 27-14-91-09 | eClass 7.1 | 27-14-91-09 |
| eClass 8.1 | 27-14-91-09 | eClass 9.0 | 27-43-03-19 |
| eClass 9.1 | 27-14-44-90 |            |             |

**Approvals**

ROHS Conform

**Downloads**

|                    |                                                                           |
|--------------------|---------------------------------------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 3 HDC 17/18 EN</a><br><a href="#">CAT 5 ENCL 17/18 EN</a> |
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>                                              |
| Engineering Data   | <a href="#">STEP</a>                                                      |

### **GWDR NP (flat gasket - neoprene)** **GWDR PG9-NP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

