GWDR NP (flat gasket - neoprene)
GWDR PG16-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR PG16-NP
Order No.	1719580000
Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 16, Neoprene
GTIN (EAN)	4008190352844
Qty.	100 pc(s).

GWDR NP (flat gasket - neoprene)
GWDR PG16-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.9 g

Width

Thickness	1.2 mm

General information

Cable glands	PG	Diameter of sealing ring	30 mm
External thread	PG 16	Inside diameter D2	22.5 mm
Material	Neoprene	O.D.	30 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-30 °C
Thickness	1.2 mm		

Classifications

ETIM 3.0	EC000781	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	31-16-18-18	eClass 5.1	23-07-90-90
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-43-03-19
eClass 9.1	27-14-44-90		

Approvals

ROHS	Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

GWDR NP (flat gasket - neoprene)
GWDR PG16-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

