

**GWDR NP (flat gasket - neoprene)
GWDR PG36-NP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR PG36-NP
Order No.	1719610000
Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 36, Neoprene
GTIN (EAN)	4008190352875
Qty.	20 pc(s).

GWDR NP (flat gasket - neoprene)
GWDR PG36-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Net weight 3.05 g

Width

Thickness 1.5 mm

General information

Cable glands	PG	Diameter of sealing ring	60 mm
External thread	PG 36	Inside diameter D2	47 mm
Material	Neoprene	O.D.	60 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-30 °C
Thickness	1.5 mm		

Classifications

ETIM 3.0	EC000781	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	31-16-18-18	eClass 5.1	23-07-90-90
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-43-03-19
eClass 9.1	27-14-44-90		

Approvals

ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

GWDR NP (flat gasket - neoprene) GWDR PG36-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

