

Accessories
EWS M 25X1,5**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Pressure-compensation elements ensure good ventilation of the enclosure and prevent the build-up of condensation while maintaining the appropriate IP class of protection.

General ordering data

Type	EWS M 25X1,5
Order No.	1719740000
Version	Compensating element, Polyamide, External thread: M 25, IP 54
GTIN (EAN)	4008190353001
Qty.	20 pc(s).

**Accessories
EWS M 25X1,5**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	23 mm	Net weight	13.25 g
--------	-------	------------	---------

Approvals

Approval for cable gland	Ex e II, II 2 GD
--------------------------	------------------

General information

AF size 1	30 mm	Cable gland	metric
Colour code	RAL 9005	External thread	M 25
Length of thread	5 mm	Material	Polyamide
Operating temperature range, max.	40 °C	Operating temperature range, min.	-20 °C
Pitch of thread	1.5 mm	Torque for connecting adapter, max.	5 Nm
Torque for connecting adapter, min.	5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09

Product information

Descriptive text technical data	Installed at the lowest point from the bottom in the wall of the enclosure Minimum enclosure wall thickness of 4 mm must be maintained.
---------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------

Datenblatt

Accessories
EWS M 25X1,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

