

Conductor markers TM 3/18 HF/HB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

Type	TM 3/18 HF/HB
Order No.	1719830000
Version	Conductor markers, 18 x 8.1 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.:
GTIN (EAN)	4008190353186
Qty.	500 pc(s).

**Conductor markers
TM 3/18 HF/HB**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	18 mm	Width	8.1 mm
Height	9.3 mm	Depth	5 mm
Net weight	0.28 g		

General data

Colour	Transparent	Material	Polyethylene LD
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	HB		

Conductor and cable markers

Conductor O.D., max.	6.5 mm	Conductor O.D., min.	4 mm
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	2.5 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform