

Conductor markers TM 4/18 HF/HB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

Type	TM 4/18 HF/HB
Order No.	1719850000
Version	Conductor markers, 18 x 11.4 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.:
GTIN (EAN)	4008190353209
Qty.	500 pc(s).

Conductor markers TM 4/18 HF/HB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	18 mm	Width	11.4 mm
Height	13.8 mm	Depth	9 mm
Net weight	0.42 g		

General data

Colour	Transparent	Material	Polyethylene LD
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	HB		

Conductor and cable markers

Conductor O.D., max.	10 mm	Conductor O.D., min.	6 mm
Conductor cross-section, max.	35 mm ²	Conductor cross-section, min.	10 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform